

ELECTRIC REFRIGERATORS MANUFACTURER  
CHECKING THE MATERIAL THICKNESS OF THIN SHEETS

MATERIAL THICKNESS GAUGES | KERN TN

Thin sheet metal is processed for the production of white goods. The thickness of the sheet has a significant influence on the quality and insulation and is therefore precisely checked upon delivery in the incoming goods department. An ultrasonic material thickness measuring device is used for this, which carries out this check very precisely and quickly



Model	Max. Pulse-Echo	Price
TN 80-0.1US	80 mm	€ 630,-
<b>Suitable Accessories:</b> <ul style="list-style-type: none"><li>● Factory calibration certificate 961-113 - 961-113 - €167,-</li></ul>		



<https://partner.kern-sohn.com/Segment/B073E-1003>

\* DAkkS calibrations are also possible on site  
All prices are net, valid until 25.10.2025 plus shipping cost

Personal consultation from our product specialist:



**Irmi Russo** Productspecialist  
Tel : +49 7433 9933-208  
[russo@kern-sohn.com](mailto:russo@kern-sohn.com)

Application number: EN - 1003

**KERN & SOHN GmbH**  
Ziegelei 1  
72336 Balingen, Germany  
[info@kern-sohn.com](mailto:info@kern-sohn.com)  
[www.kern-sohn.com](http://www.kern-sohn.com)