

PRECISION TOOLS CONSTRUCTION
CHECKING THE LAYER THICKNESS AFTER KTL PAINTING

COATING THICKNESS GAUGES | KERN TG

After the KTL painting of a workpiece, a layer thickness measuring device is used to check whether a specified layer thickness (10-50 µm) is given. This check is very important to meet the client's benchmarks



Model	Max. Coating Thickness	Readability	Price
TG 1250-0.1FN	100 µm; 1250 µm	0.1 µm; 1 µm	€ 600.-
Suitable Accessories: <ul style="list-style-type: none">● Factory calibration certificate 961-112 - 961-112 - €235.-			



<https://partner.kern-sohn.com/Segment/B063D>

* DAkkS calibrations are also possible on site
All prices plus VAT and shipping costs valid until 08.03.2026

We would be happy to advise you personally:



Irmi Russo Productspecialist
Tel : +49 7433 9933-208
russo@kern-sohn.com

Application number: EN - 1422

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com