



CAR PARTS AND CAR ACCESSORIES MANUFACTURER  
RECORDING THE EXACT AMOUNT OF GLUE TO ATTACH THE CAR HEADLINER

PRECISION BALANCES | KERN PCB

Recording the exact amount of glue to attach the car headliner, Precisely determining the amount of power adhesive is the cornerstone for secure and visually appealing attachment of the car headliner, The visual beautification of the interior, the improvement of the acoustics in the interior and also the insulation of sound penetrating from outside ensure satisfied customers



Model	Weighing capacity	Readability	Weighing surface (d)	Price
PCB 2000-1	2000 g	0.1 g	130×130 mm	€ 230.-
<b>Suitable Accessories:</b> <ul style="list-style-type: none"><li>• DAkkS calibration certificate 963-127 - 963-127 - €103.-</li></ul>				



<https://partner.kern-sohn.com/Segment/B0888>

\* DAkkS calibrations are also possible on site  
All prices plus VAT and shipping costs valid until 03.02.2026

For expert advice, please contact:



Aleksandar Delic  
Productspecialist  
Tel : +49 7433 9933-120  
aleksandar.delic@kern-sohn.com

Application number: EN - 1507

KERN & SOHN GmbH  
Ziegelei 1  
72336 Balingen, Germany  
info@kern-sohn.com  
www.kern-sohn.com