



AEROPLANES MANUFACTURER

DETERMINING THE PAINT THICKNESS OF AIRCRAFT WITH A COATING THICKNESS GAUGE

COATING THICKNESS GAUGES | KERN TG

Aircraft paintwork has a thickness of 250 microns to 300 microns with primer, adhesion promoter, base coat and top coat. In order to check the paint thickness and to be able to determine it correctly, you use a mobile layer thickness measuring device that was designed for continuous measurements or single point measurements



**NO IMAGE
AVAILABLE**

Suitable Accessories:

- Factory calibration certificate 961-112 - 961-112 -



<https://partner.kern-sohn.com/Segment/B085C>

* DAkkS calibrations are also possible on site

All prices are net, valid until 12.12.2025 plus shipping cost

Personal consultation from our product specialist:



Irmi Russo Productspecialist

Tel : +49 7433 9933-208

russo@kern-sohn.com

Application number: EN - 16 10

KERN & SOHN GmbH

Ziegelei 1

72336 Balingen, Germany

info@kern-sohn.com

www.kern-sohn.com