



PLASTIC INJECTION FOUNDRIES  
MOISTURE CONTROL OF INJECTION MOLDING GRANULATE IN INCOMING GOODS

MOISTURE ANALYSER | KERN DBS

Moist plastic granules can lead to surface defects such as streaks during the injection molding process. The moisture analyzer checks the moisture content of the granules before processing. This ensures process stability and reduces costly scrap.



Model	Weighing capacity	Readability	Price
DBS 60-3	60 g	0.001 g	€ 1,650.-
<b>Suitable Accessories:</b> <ul style="list-style-type: none"><li>• DAkkS calibration certificate 963-127 - 963-127 - €103.-</li></ul>			



<https://partner.kern-sohn.com/Segment/B0448>

\* DAkkS calibrations are also possible on site  
All prices plus VAT and shipping costs valid until 20.02.2026

For expert advice, please contact:



Aleksandar Delic  
Productspecialist  
Tel : +49 7433 9933-120  
aleksandar.delic@kern-sohn.com

Application number: EN - 1636

KERN & SOHN GmbH  
Ziegelei 1  
72336 Balingen, Germany  
info@kern-sohn.com  
www.kern-sohn.com