

TEXTILE EXPERTS
TESTING THE TENSILE STRENGTH OF YARNS

TEST STANDS (MOTORISED) | KERN TVO

When checking the quality of yarns, a tear test can be used to test the distinguishing feature of the tear strength of cotton yarns when wet (higher tear strength) and when dry. This is an elementary criterion for the quality of the yarn. The test is carried out using a so-called motorized vertical test stand



Model	Max. Force	Price
TVO 500N300	500 N	€ 2,500.-



<https://partner.kern-sohn.com/Segment/S10041>

* DAkkS calibrations are also possible on site
All prices are net, valid until 05.11.2025 plus shipping cost

Personal consultation from our product specialist:



Irmi Russo Productspecialist
Tel : +49 7433 9933-208
russo@kern-sohn.com

Application number: EN - 18 14

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com

