


ZOOLOGICAL GARDENS DETERMINATION OF RESIDUAL MOISTURE IN DRIED ALFALFA

MOISTURE ANALYSER | KERN DLB

The alfalfa, a forage crop, is chopped (30-40 mm) after cutting and dried, either in the field in warm weather or with a computer-controlled dryer. The residual moisture should not exceed 4%. This is ideally checked with a moisture analyzer. This check prevents the formation of mold in the food.



Model	Weighing capacity	Readability	Price
DLB 160-3A	160 g	0.001 g	€ 1,450.-
Suitable Accessories: <ul style="list-style-type: none">• DAkkS calibration certificate 963-127 - 963-127 - €103.-			



<https://partner.kern-sohn.com/Segment/S10786>

* DAkkS calibrations are also possible on site
All prices are net, valid until 18.01.2026 plus shipping cost

Personal consultation from our product specialist:



Aleksandar Delic
Productspecialist
Tel : +49 7433 9933-120
aleksandar.delic@kern-sohn.com

Application number: EN - 1840

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com