



METAL GRINDERS

CHECKING THE MATERIAL THICKNESS OF STAINLESS STEEL CONTAINERS AFTER THE GRINDING PROCESS

MATERIAL THICKNESS GAUGES | KERN TU

When brushing and grinding stainless steel containers, material is removed from the surface, for example to remove color differences or so-called weld beads. The material thickness is then checked, which must be of a certain size. The check serves to ensure the optimal condition of the product after the grinding process.



Model	Max. Pulse-Echo	Price
TU 80-0.01US	80 mm	€ 1,310.-
Suitable Accessories: <ul style="list-style-type: none">• Factory calibration certificate 961-113 - 961-113 - €167.-		



<https://partner.kern-sohn.com/Segment/S10477>

* DAkkS calibrations are also possible on site
All prices are net, valid until 21.01.2026 plus shipping cost

Personal consultation from our product specialist:



Irmi Russo Productspecialist
Tel : +49 7433 9933-208
russo@kern-sohn.com

Application number: EN - 1859

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com