



MANUFACTURER OF CHEMICAL-TECHNICAL PRODUCTS
DETERMINATION OF RESIDUAL MOISTURE IN A SLUDGE FILTRATE

MOISTURE ANALYSER | KERN DAB

A moisture meter can be used to determine how much residual moisture is present in a sludge filtrate. Depending on the moisture level, the operator can determine which flocculant was effective or how much flocculant needs to be used to achieve the best result.



Model	Weighing capacity	Readability	Price
DAB 200-2	200 g	0.01 g	€ 1,200.-
Suitable Accessories: <ul style="list-style-type: none">• DAkkS calibration certificate 963-127 - 963-127 - €103.-			



<https://partner.kern-sohn.com/Segment/B03E5>

* DAkkS calibrations are also possible on site
All prices are net, valid until 21.11.2025 plus shipping cost

Personal consultation from our product specialist:



Aleksandar Delic
Productspecialist
Tel : +49 7433 9933-120
aleksandar.delic@kern-sohn.com

Application number: EN - 2122

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com