

SAND FOUNDRIES  
ACCURATE WEIGHING OF SAND SAMPLES (3KG)

BENCH SCALES | KERN GAB

Sand casting is used in mechanical engineering, equipment manufacturing or in the automotive industry. The sand used for this must be put together precisely and checked again and again. For checking the water content, bulk density, compressibility, compressive strength, double shear strength, loss on ignition, etc.. 3 kg sand samples are taken. The exact weighing of the amount of sand to be tested is crucial for an exact result. Invalid search result.



Model	Weighing capacity	Readability	Price
GAB 6K0.05N	6 kg	0.00005 kg	€ 395.-
<b>Suitable Accessories:</b> <ul style="list-style-type: none"><li>• DAkkS calibration certificate 963-128 - 963-128 - €124.-</li></ul>			



<https://partner.kern-sohn.com/Segment/B0616>

\* DAkkS calibrations are also possible on site  
All prices are net, valid until 26.11.2025 plus shipping cost

Personal consultation from our product specialist:



Jürgen Fünfer  
Productspecialist  
Tel : +49 7433 9933-245  
[juergen.fuenfer@kern-sohn.com](mailto:juergen.fuenfer@kern-sohn.com)

Application number: EN - 720

KERN & SOHN GmbH  
Ziegelei 1  
72336 Balingen, Germany  
[info@kern-sohn.com](mailto:info@kern-sohn.com)  
[www.kern-sohn.com](http://www.kern-sohn.com)