




SURGICAL MACHINES MANUFACTURER
HARDNESS TESTING OF ALUMINUM SEMI-FINISHED PRODUCTS

HARDNESS TESTERS (UCI) | KERN HO

First, the alloy used must be checked for compliance with relevant standards and guidelines. A hardness tester is used to test resistance. The consistency and robustness of the material, which must comply with a specific standard, can be tested quickly and elegantly in this way in order to meet the high demands of medical technology. Invalid search result.



Model	Measuring range Rockwell - scale A	Measuring range Rockwell - scale B	Measuring range Rockwell - scale C	Price
HO 1K	37-85HRA	41-100HRB	20,3-68HRC	€ 5,520.-

Suitable Accessories:

- Factory calibration certificate 961-270 - 961-270 - €360.-

* DAkkS calibrations are also possible on site
All prices are net, valid until 14.12.2025 plus shipping cost



<https://partner.kern-sohn.com/Segment/S10014>

Personal consultation from our product specialist:



Irmi Russo Productspecialist
Tel : +49 7433 9933-208
russo@kern-sohn.com

Application number: EN - 886

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com