

TINNER SHOPS
CHECKING THE WALL THICKNESS OF GAS CYLINDERS WITH A MATERIAL THICKNESS GAUGE

MATERIAL THICKNESS GAUGES | KERN TN

Refillable pressure vessels for gases must be inspected within specified periods. The external condition (corrosion), the internal condition and the minimum wall thickness are checked. The latter is checked with a material thickness gauge. A safe, accurate and fast method.



Model	Max. Pulse-Echo	Price
TN 30-0.01EE	600 mm	€ 980.-
Suitable Accessories: <ul style="list-style-type: none">• Factory calibration certificate 961-113 - 961-113 - €167.-		



<https://partner.kern-sohn.com/Segment/B05DC>

* DAkkS calibrations are also possible on site
All prices are net, valid until 07.01.2026 plus shipping cost

Personal consultation from our product specialist:



Irmi Russo Productspecialist
Tel : +49 7433 9933-208
russo@kern-sohn.com

Application number: EN - 947

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com