

CONDITIONING SYSTEMS MANUFACTURER
DETERMINATION OF THE WATER ABSORPTION DURING THE CONDITIONING PROCESS

PRECISION BALANCES | KERN PCB

Water absorption (conditioning) is what gives dry and brittle material, such as a polyamide workpiece, its desired positive properties. The workpiece is weighed in the dry state and then again after it has been moistened in the system. The weight difference can be determined with a precision scale and thus shows the exact amount of water absorption



Model	Weighing capacity	Readability	Weighing surface (d)	Price
PCB 3000-2	3600 g	0.01 g	130×130 mm	€ 310.-
Suitable Accessories: <ul style="list-style-type: none">• DAkkS calibration certificate 963-127 - 963-127 - €103.-				



<https://partner.kern-sohn.com/Segment/S10469>

* DAkkS calibrations are also possible on site
All prices are net, valid until 17.01.2026 plus shipping cost

Personal consultation from our product specialist:



Aleksandar Delic
Productspecialist
Tel : +49 7433 9933-120
aleksandar.delic@kern-sohn.com

Application number: EN - 954

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen, Germany
info@kern-sohn.com
www.kern-sohn.com